

Hot insulated double & triple door cabinets for insulated trays for correctional facilities with top mounted heating unit.

390-A Meyer Circle • Corona, CA 92879-1078 • Phone (951) 340-3419 • Fax (951) 340-2716 • www.sammonseguipment.com

- Fully insulated hot s/s cabinets.(Double or triple doors)
- Top mounted heating unit with 1600W heating & 15 amps cord & NEMA 5-15P plug for double door cabinets .2000W heating with 20 amps cord & NEMA 5-plug for 3 door cabinets.(optional for 2 door cabinets).
- 6"x 2" swivel casters, 2 with brakes, push handle & perimeter bumper are standard.

These cabinets are furnished with 1½" fiberglass insulation. The top mounted heating unit is easily removable (non removable optional) & provides the necessary gentle & forced air circulation with thermostatically controlled temperature.


Outer body, door & top are made of 20 ga. (18 ga. optional) polished stainless steel for strength & durability. Push handle. 14 ga. s/s reinforced deck, perimeter bumper, tramper resistant fasteners, heavy duty latches and 12 ga. s/s reinforced correctional hinges are standard.

HET-1600 Heating unit:

1600W heating coil, 1,750w total, 14.58 apms to 120VAC 60HZ single phase furnished with 15 amps, 8ft. long cord with 3 prong Nema 5-15 grounding plug, switch off-on switch, two 75w blowers, thermostat, pilot lights and dial thermometer. Blower and heating coils are thermally protected. Optional 220-240-V available. Optional HET-2000 heating unit with 2000w heating coil, 2150W total, 17.92 amps and 20 amp cord, and 5-20P plug for 20 amps service is also available (standard for triple door cabinet). Consult factory



| Model Number | Tray Spacing (Inches) | Type of | Tray Capacity | O.A. Dimensions (Inches) | | | Weight |
|--------------------|--------------------------------------|------------|------------------|-----------------------------|-------|-------|----------|
| | | Door | | D | W | Н | (Pounds) |
| 2287-HIN-2-1116-40 | 11X16X2¾ (T-140) SEE NOTE 2 | Double | 40 | 311/2 | 481/2 | 525/8 | 405 |
| 2287-HIN-2-1116-52 | | Double | 52 | 311/2 | 481/2 | 585/8 | 430 |
| 2287-HIN-2-1116-60 | | Double | 60 | 311/2 | 481/2 | 645/8 | 450 |
| 2287-HIN-3-1116-66 | | Triple | 66 | 311/2 | 69¾ | 525/8 | 490 |
| 2287-HIN-3-1116-90 | | Triple | 90 | 311/2 | 69¾ | 645/8 | 580 |
| 2287-HIN-3-1116-96 | | Triple | 96 | 311/2 | 69¾ | 681/4 | 596 |
| 2287-HIN-2-1315-44 | 13%"x15½"x2½" (ALLADIN) SEE NOTE 3 | Double | 44 | 371/4 | 481/2 | 525/8 | 390 |
| 2287-HIN-2-1315-56 | | Double | 56 | 371/4 | 481/2 | 585/8 | 460 |
| 2287-HIN-2-1315-66 | | Triple | 66 | 371/4 | 69¾ | 525/8 | 625 |
| 2287-HIN-2-1315-92 | | Triple | 92 | 371/4 | 69¾ | 645/8 | 650 |



Note 2: These models for 11"x16x2¾" trays will also carry Duralux T-240 (11¼"x15½"x2 2/5" thk.), Incellator #2 & 3 (10"x16"x2.15" or 2.85" thk.), Plastocon (10¾"x14½"x2½" or 3¼"thk.), and Rock (9½"x14¼"x1½" thk.) trays. Capacity will vary.

Note 3: These models for 13%"x15½"x2½" will NOT go thru a standard 33" W door. Please make sure that you hallway door openings are larger than 38" for these carts. These models will also carry design specialty T-340 (13%"x15½"x2½"₁₆" thk.) and Plastocon (Insulator & Supermax 13.6"x15"x2.86" thk.) trays. Capacity will vary. Sample tray is required with order for proper sizing

Options:

- Correctional package
- 2. Lockable hasps
- 3. 18 ga. Exterior

Options:

- 4. 6" Balloon casters upgrade
- 5. 8" Balloon casters upgrade
- 6. 8" Polyurethane casters upgrade



2287-HIN-2-1116-60 (shown with correction package)



2287-HIN-3-1116-90 (shown with correctional package)